

Proximity sensor SME-8-K5-LED-24

Part number: 175404

FESTO



General operating condition

Data sheet

Feature	Value
Design	For T-slot
Conforms to standard	EN 60947-5-2
Symbol	00991620
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Note on materials	RoHS compliant
Application note	Support / actuator-sensor overview "The right sensor for the actuator"
Measured variable	Position
Measuring principle	Magnetic reed
Ambient temperature	-40 °C ... 70 °C
Repetition accuracy	0.2 mm
Switching output	Contact-based, bipolar
Switching element function	N.O. contact
On time	≤0.5 ms
Switch-off time	0.03 ms
Max. switching frequency	800 Hz
Max. output current	500 mA
Min. switching capacity AC	10 VA
Max. switching capacity DC	10 W
Voltage drop	0 V
Inductive protective circuit	Adapted to MZ, MY and ME coils
Short-circuit protection	No
Overload protection	Not available
Operating voltage range AC	12 V ... 30 V
DC operating voltage range	12 V ... 30 V
Reverse polarity protection	No
Electrical connection 1, connection type	Cable
Electrical connection 1, connection technology	Open end
Electrical connection 1, number of pins/wires	3
Connection outlet orientation	Longitudinal
Cable length	5 m
Color cable sheath	Gray
Material of cable sheath	TPE-U(PUR)

Feature	Value
Type of mounting	Clamped in T slot Can be inserted in slot lengthwise
Tightening torque	0.2 Nm
Mounting position	Any
Product weight	60 g
Housing colour	Black
Housing material	PC PET high-alloy stainless steel
Switching status indication	Yellow LED
Ambient temperature with flexible cable installation	-5 °C ... 70 °C
Degree of protection	IP65 IP67
Insulation voltage	50 V
Surge resistance	0.8 kV
LABS (PWIS) conformity	VDMA24364-B2-L
Contamination level	3