


Motor flange EAMF-A-44A-60G/H

Part number: 1780430

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C ... 60 °C
Product weight	178 g
Interface code, motor in	60G 60H
Interface code, coupling housing	44A
Note on materials	RoHS-compliant