

ISO cylinder DSBF-C-80-500-PPSA-N3-R

Part number: 1781072

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Stroke	500 mm
Piston diameter	80 mm
Piston rod thread	M20x1.5
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	Any
Conforms to standard	ISO 15552
Piston rod end	External thread
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Symbol	00991235
Operating pressure	0.04 MPa ... 1.2 MPa
Operating pressure	0.4 bar ... 12 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	1.8 J
Cushioning length	31 mm
Theoretical force at 6 bar, retracting	2721 N
Theoretical force at 6 bar, advancing	3016 N
Moving mass	2750 g
Moving mass at 0 mm stroke	800 g
Additional moving mass per 10 mm stroke	39 g
Product weight	7881 g
Basic weight with 0 mm stroke	3131 g
Additional weight per 10 mm stroke	95 g
Type of mounting	With internal thread With accessories
Pneumatic connection	G3/8
Note on materials	RoHS-compliant
Cover material	Die-cast aluminum, coated
Piston seal material	TPE-U(PU)

Feature	Value
Material of piston	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel
Piston rod wiper material	TPE-U(PU)
Buffer seal material	TPE-U(PU)
Cushion piston material	POM
Material of cylinder barrel	Wrought aluminum alloy, anodized
Nut material	High-alloy stainless steel
Material of bearing	POM
Flange screws material	Steel, galvanized