

# Proximity sensor SIES-Q8B-NS-S-L

Part number: 178293

FESTO



[PDF](#) General operating condition

## Data sheet

Feature	Value
Conforms to standard	EN 60947-5-2
Symbol	00991703
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	according to UK RoHS regulations (UK-R)
Note on materials	RoHS compliant
Rated operating distance	1.5 mm
Assured operating distance	1.2 mm
Reduction factors	Aluminum = 0.45 Stainless steel St 18/8 = 0.8 Copper = 0.4 Brass = 0.55 Steel St 37 = 1.0
Ambient temperature	-25 °C ... 70 °C
Repetition accuracy	0.07 mm
Switching output	NPN
Switching element function	N.O. contact
Max. switching frequency	3500 Hz
Max. switching frequency DC	1500 Hz
Max. output current	200 mA
Voltage drop	2 V
Short-circuit protection	Pulsed
DC operating voltage range	10 V ... 30 V
Residual ripple	10%
Idle current	≤10 mA
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	not rotatable
Electrical connection 1, type of mounting	Compatible with snap-locking Compatible with rotatable screw-type lock
Size	8x8x59 mm
Type of mounting	With internal thread
Mounting type	Flush
Product weight	12 g

<b>Feature</b>	<b>Value</b>
Housing material	Die-cast zinc Chrome-plated Nickel-plated
Switching status indication	Yellow LED
Degree of protection	IP67
LABS (PWIS) conformity	VDMA24364-B2-L
Selection of additional sensor information	Special design
Electrical output	NPN
Selection of sensor version	Standard