

Valve manifold CPV10-VI

Part number: 18200

FESTO



 General operating condition

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Electrical actuation	AS-Interface CPI installation system Individual connection Fieldbus Multi-pin
Electrical I/O system	Yes
Valve terminal type	10
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-5 °C ... 50 °C
Ambient temperature	-5 °C ... 50 °C
Storage temperature	-20 °C ... 40 °C
Degree of protection	IP65
Corrosion resistance class (CRC)	1 - Low corrosion stress 2 - Moderate corrosion stress
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Information on operating pressure	0 – 0.8 bar with external pilot air 0 - 8 bar with external pilot air
Pilot pressure MPa	0.3 MPa ... 0.8 MPa
Pilot pressure	3 bar ... 8 bar
LABS (PWIS) conformity	VDMA24364-B1/B2-L
CE marking (see declaration of conformity)	As per EU EMC directive as per EU explosion protection directive (ATEX) As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
KC characters	KC-EMV
Certification	RCM compliance mark c UL us - recognized (OL)
Explosion prevention and protection	Class I, Div. 2 (US) Zone 2 (ATEX) Zone 2 (UKEX)
ATEX category gas	II 3G
Explosion protection certification outside the EU	EPL Gc (GB) NEC 500 Class I, Div. 2

Feature	Value
Type of ignition protection for gas	Ex ec IIC T4 Gc X
Explosive ambient temperature	-5°C ≤ Ta ≤ +50°C
Note on materials	RoHS compliant
Valve manifold design	Fixed grid
Max. no. of valve positions	8
Max. no. of valve functions	16
Max. no. of pressure zones	2
Actuation type	Electrical
Valve function	Vacuum generator Vacuum generator + 2/2, closed, monostable
Structural design	Piston gate valve
Sealing principle	Soft
Valve size	10 mm
Pilot air supply port	External Internal
Max. standard nominal flow rate	400 l/min at 10 mm
Nominal width	4 mm
Suitability for vacuum	Yes
Pneumatic working port	M7 QS-4 QS-6 QS-1/8 QS-1/4
Pneumatic connection 1	Common connection
Pneumatic connection 2	M7
Pneumatic connection 3	Common connection
Pneumatic connection 4	M7
Pilot air port 12/14	Common connection
Pilot exhaust air port 82/84	Common connection
Signal status display	LED
Nominal operating voltage DC	24 V