

Angled gripper HGWM-08-EO-G8

Part number: 185695

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	8
Max. gripper jaw angular play ax, ay	0.5 deg
Max. gripper jaw backlash Sz	0.03 mm
Max. opening angle	17 deg
Pneumatic gripper repetition accuracy	≤0.02 mm
Number of gripper jaws	2
Actuator system	Pneumatic
Mode of operation	Single-acting Open
Gripper function	Angle
Gripping force backup	Without
Structural design	Inclined plane
Position sensing	None
Symbol	00991897
Operating pressure	2 bar ... 8 bar
Max. operating frequency of pneumatic gripper	4 Hz
Min. opening time at 6 bar	2.7 ms
Min. closing time at 6 bar	1.2 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	5 °C ... 60 °C
Spring return torque	0.005 Nm
Total gripping torque at 6 bar, closing	22 Ncm
Mass moment of inertia	25.2 kgcm ²
Mass moment of inertia per external gripper finger	250 kgcm ²
Maximum force on gripper jaw Fz, static	7 N
Maximum torque on gripper jaw, Mx static	0.2 Nm
Maximum torque on gripper jaw, My static	0.2 Nm
Maximum torque on gripper jaw, Mz static	0.2 Nm
Max. mass per external gripper finger	400 g
Product weight	13 g
Type of mounting	Clamped
Pneumatic connection	M3
Note on materials	RoHS-compliant

Feature	Value
Cover cap material	POM
Housing material	High-alloy stainless steel
Gripper jaw material	High-alloy steel