

Rotary actuator DSM-10-240-P-A-FF-FW

Part number: 185947

FESTO



 General operating condition

Data sheet

Feature	Value
Size	10
Cushioning angle	0 deg
Adjustment range of swivel angle	0 deg ... 200 deg
Swivel angle	0 deg ... 200 deg
Permissible stop radius	≥13 mm
Mounting position	Any
Precision adjustment	-5 deg
Mode of operation	Double-acting
Structural design	Rotary vane
Position sensing	For proximity sensor
Symbol	00991265
Operating pressure	0.25 MPa ... 0.8 MPa
Operating pressure	2.5 bar ... 8 bar
Max. swivel frequency at 6 bar	2 Hz
Repetition accuracy	1 deg
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C ... 60 °C
Max. stop force	60 N
Max. axial force	10 N
Max. radial force	30 N
Theoretical torque at 6 bar	0.85 Nm
Permissible mass moment of inertia	0.0026 kgm ²
Product weight	265 g
Type of mounting	With internal thread
Pneumatic connection	M3
Covering material	PA-reinforced
Note on materials	RoHS-compliant
Drive shaft material	High-alloy stainless steel
Seals material	TPE-U(PU)
Housing material	Anodized