

Vacuum suction cup ESS-200-SN

Part number: 189330

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|--|
| Min. workpiece radius | 680 mm |
| Nominal width | 10 mm |
| Suction cup diameter | 200 mm |
| Suction cup volume | 245.454 cm ³ |
| Connection position | Top |
| Mounting position | Any |
| Symbol | 00991485 |
| Classification of suction cup holder | Size 6 |
| Suction cup shape | Round, flat |
| Operating pressure | -0.095 MPa ... 0 MPa |
| Operating pressure | -0.95 bar ... 0 bar |
| Operating pressure | -13.775 psi ... 0 psi |
| Nominal operating pressure | -0.07 MPa |
| Nominal operating pressure | -0.7 bar |
| Nominal operating pressure | -10.15 psi |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| For use in the food industry | See supplementary material information |
| Ambient temperature | -10 °C ... 70 °C |
| Holding force at nominal operating pressure | 1610 N |
| Lateral force at nominal operating pressure | 850 N |
| Product weight | 1198 g |
| Type of mounting | Via vacuum connection |
| Vacuum connection | M20x2 |
| Color | Black |
| Shore hardness | 50 +/- 5 |
| Material of screwed plug | NBR Steel, nickel-plated Steel, galvanized and chrome-plated |
| Note on materials | RoHS-compliant |

| Feature | Value |
|----------------------|-------|
| Suction cup material | NBR |