

Short-stroke cylinder AEVC-4-2,5-P

Part number: 188050

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Stroke	2.5 mm
Piston diameter	4 mm
Spring resetting force with piston rod in retracted position	1 N
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Pushing Single-acting
Structural design	Piston Piston rod
Position sensing	None
Symbol	00991730
Operating pressure	0.25 MPa ... 0.8 MPa
Operating pressure	2.5 bar ... 8 bar
Operating pressure	36.25 psi ... 116 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 80 °C
Theoretical force at 6 bar, advancing	4.9 N
Moving mass	0.15 g
Product weight	3 g
Type of mounting	With through-hole With accessories
Pneumatic connection	M3
Note on materials	RoHS compliant
Cover material	Wrought aluminum alloy Anodized
Seals material	HNBR NBR
Housing material	Anodized
Piston rod material	Wrought aluminum alloy Anodized