

Ball valve actuator unit VZBA-3/4"-GGG-63-32L-F0405-V4V4T-PP30-R-90-C

FESTO

Part number: 1914788



General operating condition

Data sheet

| Feature | Value |
|--|--|
| Structural design | L bore |
| Actuation type | Pneumatic |
| Mounting position | Any |
| Type of mounting | In-line installation |
| Fitting connection | Rp3/4 |
| Switching position indication | Slot direction = flow direction |
| Nominal width DN | 20 |
| Operating pressure | 6 bar ... 8.4 bar |
| Nominal pressure of fitting PN | 63 |
| Symbol | 00995329 |
| Medium | Compressed air as per ISO 8573-1:2010 [:-:-] Inert gas Water – no water vapor Neutral liquids |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Temperature of medium | -10 °C ... 200 °C |
| Ambient temperature | -10 °C ... 80 °C |
| Flow rate Kv type L | 5.1 m ³ /h |
| Max. surface temperature of assembly | TX |
| Explosion group of assembly | IIC, IIIC |
| Note on materials | RoHS compliant |
| LABS (PWIS) conformity | VDMA24364 Zone III |
| Housing material | high-alloy stainless steel |
| Material number of housing | 1,4408 |
| Seals material | PTFE PTFE-reinforced |
| Ball material | high-alloy stainless steel |
| Material number for ball | 1,4408 |
| Shaft material | high-alloy stainless steel |
| Material number for shaft | 1,4401 |
| Product weight | 2050 g |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |

| Feature | Value |
|----------------------------------|---------------------------|
| Explosive ambient temperature | -10°C ≤ Ta ≤ +60°C |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |