

# ISO cylinder DNC-80-150-PPV-A

Part number: 1922645

FESTO



[PDF](#) General operating condition

## Data sheet

| Feature                                  | Value  |
|--|--|
| Stroke                                   | 150 mm   |
| Piston diameter                          | 80 mm  |
| Piston rod thread                        | M20x1.5  |
| Cushioning                               | Pneumatic cushioning, adjustable at both ends                      |
| Mounting position                        | Any  |
| Conforms to standard                     | ISO 15552  |
| Piston rod end                           | External thread  |
| Structural design                        | Piston<br>Piston rod<br>Profile barrel                             |
| Position sensing                         | For proximity sensor   |
| Symbol                                   | 00991235   |
| Variants                                 | Piston rod at one end  |
| Operating pressure                       | 0.06 MPa ... 1.2 MPa   |
| Operating pressure                       | 0.6 bar ... 12 bar   |
| Mode of operation                        | Double-acting  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Ambient temperature                      | -20 °C ... 80 °C   |
| Impact energy in the end positions       | 0.9 J  |
| Cushioning length                        | 32 mm  |
| Theoretical force at 6 bar, retracting   | 2721 N   |
| Theoretical force at 6 bar, advancing    | 3016 N   |
| Moving mass at 0 mm stroke               | 1131 g   |
| Additional moving mass per 10 mm stroke  | 38 g   |
| Basic weight with 0 mm stroke            | 2790 g   |
| Additional weight per 10 mm stroke       | 106 g  |
| Type of mounting                         | With internal thread<br>With accessories                           |
| Pneumatic connection                     | G3/8   |
| Note on materials                        | RoHS-compliant   |
| Cover material                           | Die-cast aluminum<br>Coated  |
| Seals material                           | TPE-U(PU)  |

| <b>Feature</b>              | <b>Value</b>                              |
|-----------------------------|---|
| Piston rod material         | High-alloy steel                          |
| Material of cylinder barrel | Wrought aluminum alloy<br>Smooth anodized |