

# Micro filter LFMA-D-MAXI

Part number: 192565

FESTO



 General operating condition

## Data sheet

Feature	Value
Series	D
Size	Maxi
Structural design	Fiber filter
Grade of filtration	0.01 µm
Condensate drain	Manually rotating
Symbol	00991519
Operating pressure	1 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gases
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [1:7:2] Inert gas
Filter efficiency	99.99 %
Bowl guard	Metal bowl guard
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	5 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Filter efficiency, fine particles	99995 %
MPPS	0.05 µm
MPPS filter efficiency	99.95 %
Residual oil content	0.01 mg/m <sup>3</sup>
Filter efficiency, oil aerosol	99 %
Type of mounting	With accessories
Mounting position	Vertical +/- 5°
Pneumatic connection 1	Sub-base
Pneumatic connection 2	Sub-base
Housing material	Die-cast zinc
Compressed air filter material	Borosilicate fiber
Material of bowl	PC
Note on materials	RoHS-compliant