

Service unit FRC-3/8-D-5M-O-MINI-A

Part number: 192662

FESTO



Data sheet



[PDF](#) General operating condition

| Feature | Value |
|---------------------------------------------------|--------------------------------------------------------------------|
| Size | Mini |
| Series | D |
| Actuator lock | Rotary knob with detent |
| Mounting position | Vertical $\pm 5^\circ$ |
| Condensate drain | Fully automatic |
| Structural design | Proportional standard oil mist lubricator |
| Max. condensate volume | 22 ml |
| Grade of filtration | 5 μm |
| Bowl guard | Metal bowl guard |
| Symbol | 00991546 |
| Pressure gauge | Set up for G1/8 |
| Operating pressure | 0.2 MPa ... 1.2 MPa |
| Operating pressure | 2 bar ... 12 bar |
| Pressure regulation range | 0.5 bar ... 12 bar |
| Max. pressure hysteresis | 0.02 MPa |
| Max. pressure hysteresis | 0.2 bar |
| Max. pressure hysteresis | 2.9 psi |
| Normal nominal flow rate (normalized to DIN 1343) | 1050 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gases |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [6:8:-] Inert gases |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 660 g |
| Type of mounting | With accessories |
| Pneumatic connection 1 | G3/8 |
| Pneumatic connection 2 | G3/8 |
| Note on materials | RoHS compliant |
| Housing material | Die-cast zinc |
| Material of bowl | PC |