

Vacuum generator VN-07-M-T3-PI4-VI4-RO1

Part number: 193549

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|--|
| Nominal width of Laval nozzle | 0.7 mm |
| Width dimension | 14 mm |
| Muffler construction type | Open |
| Mounting position | Any |
| Ejector characteristics | High vacuum Inline |
| Integrated function | Muffler open |
| Structural design | T-shape |
| Symbol | 00991488 |
| Operating pressure for max. suction rate | 7 bar |
| Operating pressure | 1 bar ... 8 bar |
| Operating pressure for max. vacuum | 5.8 bar |
| Max. vacuum | 86 % |
| Nominal operating pressure | 6 bar |
| Max. suction rate with respect to atmosphere | 13.5 l/min |
| Air supply time at nominal operating pressure | 2.1 s |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication not possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | 0 °C ... 60 °C |
| Noise level at nominal operating pressure | 59 dB(A) |
| Ambient temperature | 0 °C ... 60 °C |
| Max. tightening torque | 0.5 Nm |
| Product weight | 24 g |
| Type of mounting | With through-hole With accessories |
| Pneumatic connection 1 | G1/8 |
| Pneumatic connection 3 | Muffler open |
| Vacuum connection | G1/8 |
| Material of connecting thread | Wrought aluminum alloy, anodized Brass, nickel-plated |
| Note on materials | RoHS compliant |
| Seals material | NBR |

| Feature | Value |
|------------------------|------------------------|
| Female nozzle material | POM |
| Housing material | Reinforced POM |
| Muffler material | Protective grounding |
| Material of jet nozzle | Wrought aluminum alloy |