


Vacuum generator VN-20-L-T6-PQ4-VQ5-R02

Part number: 193578

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Nominal width of Laval nozzle	2 mm
Width dimension	24 mm
Muffler construction type	Open
Mounting position	Any
Ejector characteristics	High suction flow Standard
Integrated function	Muffler open
Structural design	T-shape
Symbol	00991489
Operating pressure for max. suction rate	3 bar
Operating pressure	1 bar ... 8 bar
Nominal operating pressure	6 bar
Max. suction rate with respect to atmosphere	188 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Temperature of medium	0 °C ... 60 °C
Noise level at nominal operating pressure	60 dB(A)
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	0.8 Nm
Product weight	182 g
Type of mounting	With through-hole With accessories
Pneumatic connection 1	QS-10
Pneumatic connection 3	Muffler open
Vacuum connection	QS-12
Note on materials	RoHS compliant
Seals material	NBR
Female nozzle material	POM
Housing material	Reinforced POM
Muffler material	Die-cast aluminum POM PU foam
Material of jet nozzle	Wrought aluminum alloy
Material of pneumatic fitting	Brass Nickel-plated