

Vacuum generator VN-05-N-I3-PQ2-VT2

Part number: 193637

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Nominal width of Laval nozzle	0.45 mm
Width dimension	13 mm
Mounting position	Any
Ejector characteristics	High suction rate Inline
Structural design	Straight design
Symbol	00991491
Operating pressure for max. suction rate	6 bar
Operating pressure	1 bar ... 8 bar
Nominal operating pressure	6 bar
Max. suction rate with respect to atmosphere	12 l/min
Air supply time at nominal operating pressure	1.57 s
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	0 °C ... 60 °C
Ambient temperature	0 °C ... 60 °C
Product weight	12 g
Type of mounting	Line installation
Pneumatic connection 1	QS-6
Pneumatic connection 3	Not ducted
Vacuum connection	Push-in sleeve QS-6
Note on materials	RoHS-compliant
Seals material	NBR
Female nozzle material	POM
Housing material	POM-reinforced
Material of jet nozzle	Wrought aluminum alloy
Material of pneumatic fitting	Brass Nickel-plated