

Vacuum generator VN-05-L-T3-PQ2-VA4-R01

Part number: 193609

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Nominal width of Laval nozzle	0.45 mm
Width dimension	14 mm
Muffler construction type	Open
Mounting position	Any
Ejector characteristics	High suction flow Standard
Integrated function	Muffler open
Structural design	T-shape
Symbol	00991489
Operating pressure for max. suction rate	5 bar
Operating pressure	1 bar ... 8 bar
Nominal operating pressure	6 bar
Max. suction rate with respect to atmosphere	15.7 l/min
Air supply time at nominal operating pressure	1.7 s
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	0 °C ... 60 °C
Noise level at nominal operating pressure	53 dB(A)
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	0.5 Nm
Product weight	26 g
Type of mounting	With through-hole With accessories
Pneumatic connection 1	QS-6
Pneumatic connection 3	Muffler open
Vacuum connection	G1/8
Material of connecting thread	Wrought aluminum alloy Brass, nickel-plated
Note on materials	RoHS compliant
Seals material	NBR
Female nozzle material	POM
Housing material	Reinforced POM
Muffler material	Protective grounding
Material of jet nozzle	Wrought aluminum alloy

Feature	Value
Material of pneumatic fitting	Brass Nickel-plated