

Pressure regulator LRS-1/4-D-7-I-MIDI

Part number: 194631

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Size | Midi |
| Series | D |
| Actuator lock | Rotary knob with integrated lock |
| Mounting position | Any |
| Structural design | Directly controlled diaphragm regulator |
| Controller function | Constant output pressure With primary pressure compensation With secondary exhausting With return flow characteristic |
| Symbol | 00991558 |
| Pressure gauge | with pressure gauge |
| Operating pressure | 0 MPa ... 1.6 MPa |
| Operating pressure | 0 bar ... 16 bar |
| Pressure regulation range | 0.5 bar ... 7 bar |
| Max. pressure hysteresis | 0.02 MPa |
| Max. pressure hysteresis | 0.2 bar |
| Max. pressure hysteresis | 2.9 psi |
| Normal nominal flow rate (normalized to DIN 1343) | 2200 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 1250 g |
| Type of mounting | With accessories |
| Pneumatic connection 1 | G1/4 |
| Pneumatic connection 2 | G1/4 |
| Note on materials | RoHS compliant |
| Material of sub-base | Die-cast zinc |
| Seals material | NBR |
| Housing material | Die-cast zinc |