


# Bus node CPX-FB13

Part number: 195740

FESTO



 General operating condition

## Data sheet

Feature	Value
Protocol	Profibus DP
Dimensions W x L x H	50 mm x 107 mm x 50 mm
Product weight	115 g
Ambient temperature	-5 °C ... 50 °C
Storage temperature	-20 °C ... 70 °C
Degree of protection	IP65 IP67
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PC
LED display (product-specific)	M: Modify, parameterization PL: Load supply PS: electronics supply, sensor supply SF: System fault
LED display (bus-specific)	BF: Bus error
Device-specific diagnostics	Channel-oriented and module-oriented diagnostics Undervoltage of modules Diagnostic memory
Control elements	DIL switch
Fieldbus interface	2x M12x1, 5-pin, B-coded Sub-D socket, 9-pin Customizable Sub-D plug
Max. address capacity inputs	64 byte
Max. address capacity outputs	64 byte
Parameterization	Diagnostic behavior Fail-safe response forcing of channels Signal setup System Parameters
Baud rate	96 ... 12000 kbit/s
Configuration support	GSD file
Additional functions	Channel-based diagnostics via fieldbus Start-up parameterization in plain text via fieldbus System status can be indicated via process data Additional diagnostic interface for operator units
DC operating voltage range	18 V ... 30 V
Nominal operating voltage DC	24 V
Intrinsic current consumption at nominal operating voltage	Type. 200 mA
Communication types	DPV0: Cyclic communication DPV1: Acyclic communication