

Rod eye CRSGS-M16X1,5

Part number: 195584

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Size | M16x1.5 |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils. |
| Ambient temperature | -40 °C ... 150 °C |
| Max. load capacity | 4 kN |
| Product weight | 265 g |
| Note on materials | RoHS-compliant |
| Material of outer ring | High-alloy steel |
| Housing material | High-alloy steel |
| Inner raceway material | High-alloy steel |
| Nut material | High-alloy steel |