

Parallel gripper HGPM-08-EO-G6

Part number: 197559

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Size | 8 |
| Stroke per gripper jaw | 2 mm |
| Max. interchangeability | 0.2 mm |
| Max. gripper jaw angular play ax, ay | <0.5 deg |
| Max. gripper jaw backlash Sz | <0.03 mm |
| Pneumatic gripper repetition accuracy | ≤0.05 mm |
| Number of gripper jaws | 2 |
| Actuator system | Pneumatic |
| Mode of operation | Single-acting Open |
| Gripper function | Parallel |
| Gripping force backup | Without |
| Structural design | Inclined plane |
| Position sensing | None |
| Symbol | 00991897 |
| Operating pressure | 4 bar ... 8 bar |
| Max. operating frequency of pneumatic gripper | 4 Hz |
| Min. opening time at 6 bar | 4.9 ms |
| Min. closing time at 6 bar | 2.3 ms |
| Max. mass per external gripper finger | 5 g |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | 5 °C ... 60 °C |
| Stroke compensation spring force | 4 N ... 6 N |
| Gripping force per gripper jaw at 6 bar, opening | 16 N |
| Gripping force per gripper jaw at 6 bar, closing | 8 N |
| Mass moment of inertia | 0.00922 kgcm ² |
| Maximum force on gripper jaw Fz, static | 10 N |
| Maximum torque on gripper jaw, Mx static | 0.1 Nm |
| Maximum torque on gripper jaw, My static | 0.1 Nm |
| Maximum torque on gripper jaw, Mz static | 0.1 Nm |
| Product weight | 19 g |
| Type of mounting | With through-hole |

| Feature | Value |
|----------------------|----------------------------------|
| Pneumatic connection | M3 |
| Note on materials | RoHS-compliant |
| Cover cap material | POM |
| Housing material | Wrought aluminum alloy, anodized |
| Gripper jaw material | High-alloy steel |