

Feed separator HPVS-22-60-A

Part number: 2095363

FESTO



 General operating condition

Data sheet

Feature	Value
Stroke	60 mm
Piston diameter	22 mm
Max. interchangeability	0.3 mm
Max. tappet play Sx	0.05 mm
Max. tappet play Sz	0.03 mm
Max. gripper jaw angular backlash	0.04 deg
Max. gripper jaw angular backlash ay	0.07 deg
Max. gripper jaw angular backlash az	0.12 deg
External finger mounting	Through-hole
Cushioning	No cushioning
Mounting position	Any
Mode of operation	Double-acting
Structural design	Piston rod Anti-twist feature
Position sensing	Via proximity switch
Symbol	00991216
Protection against torsion/guide	Rectangular guide
Minimum product distance due to proximity switches	70 mm ... 120 mm
Proximity switch protrusion	14 mm ... 22 mm
Operating pressure	3 bar ... 8 bar
Advancing time	480 ms ... 960 ms
Retracting time	480 ms ... 960 ms
Repetition accuracy	0.25 mm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP40
Ambient temperature	5 °C ... 60 °C
Max. tightening torque	24 Nm for M8 9.9 Nm for M6
Max. force on finger Fz static	180 N
Max. static moment Mr at finger	9 Nm
Max. static moment Mx at finger	9 Nm
Max. static moment at finger	9 Nm
Theoretical force at 6 bar, retracting	180 N

Feature	Value
Theoretical force at 6 bar, advancing	225 N
Product weight	1000 g
Max. mass per external gripper finger	395 g
Alternative connections	M5
Type of mounting	with through-hole for M6 screw and centering sleeve with internal thread M8 and centering sleeve
Pneumatic connection	M5
Note on materials	RoHS compliant
Cover material	High-alloy steel
Seals material	NBR
Housing material	Wrought aluminum alloy, smooth-anodized
Piston rod material	High-alloy steel
Plunger material	High-alloy steel
Material gate valve	Case-hardened steel