

ISO cylinder DSBG-160-200-P-N3

Part number: 2536754

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Stroke | 200 mm |
| Piston diameter | 160 mm |
| Piston rod thread | M36x2 |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Conforms to standard | ISO 15552 |
| Piston rod end | External thread |
| Structural design | Piston Piston rod Tie rod Cylinder barrel |
| Symbol | 00991227 |
| Variants | Piston rod at one end |
| Operating pressure | 0.06 MPa ... 1 MPa |
| Operating pressure | 0.6 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 3.3 J |
| Theoretical force at 6 bar, retracting | 11310 N |
| Theoretical force at 6 bar, advancing | 12064 N |
| Moving mass | 6232 g |
| Moving mass at 0 mm stroke | 4292 g |
| Additional moving mass per 10 mm stroke | 97 g |
| Product weight | 15911 g |
| Basic weight with 0 mm stroke | 11751 g |
| Additional weight per 10 mm stroke | 208 g |
| Type of mounting | With internal thread With accessories |
| Pneumatic connection | G3/4 |
| Note on materials | RoHS-compliant |
| Cover material | Die-cast aluminum, coated |
| Piston seal material | NBR |
| Material of piston | Cast aluminum |

| Feature | Value |
|-----------------------------|---|
| Piston rod material | High-alloy steel |
| Piston rod wiper material | NBR |
| Buffer seal material | TPE-U(PU) |
| Cushion piston material | POM |
| Material of cylinder barrel | Wrought aluminum alloy, smooth-anodized |
| Nut material | Steel, galvanized |
| Material of bearing | Metal polymer compound |
| Collar nut material | Steel, galvanized |
| Tie rod material | High-alloy steel |