

Position sensor SRBS-Q12-40-E270-EP-1-S-M8

Part number: 2393550

FESTO



General operating condition

Data sheet

| Feature | Value |
|--|---|
| Design | Round |
| Based on norm | EN 60947-5-2 |
| Symbol | 00995400 |
| Certification | RCM compliance mark c UL us - Listed (OL) |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| Special features | Oil-resistant |
| Note on materials | RoHS-compliant Halogen-free |
| Measured variable | Rotation angle |
| Measuring principle | Magnetic Hall |
| Sensing range | >270 deg |
| Ambient temperature | -20 °C ... 70 °C |
| Typical sampling interval | 3 ms |
| Switching output | 2 x PNP or 2 x NPN switchable |
| Switching element function | N/C contact/N/O contact switchable |
| Switching point reproducibility | ≤ 1° |
| On time | ≤ 4 ms |
| Switch-off time | ≤ 4 ms |
| Max. switching frequency | 125 Hz |
| Max. output current | 50 mA |
| Max. switching capacity DC | 1.5 W |
| Voltage drop | ≤ 1 V |
| Residual current | ≤ 0.05 mA |
| Short-circuit protection | yes |
| Overload protection | Yes |
| Rated operating voltage DC | 24 V |
| DC operating voltage range | 10 V ... 30 V |
| Residual ripple | 10 % |
| Idle current | ≤ 20 mA |
| Reverse polarity protection | for all electrical connections |
| Electrical connection 1, connection type | Cable with plug |
| Electrical connection 1, connection technology | M8x1 A-coded as per EN 61076-2-104 |
| Electrical connection 1, number of pins/wires | 4 |

| Feature | Value |
|---|--|
| Electrical connection 1, type of mounting | rotatable |
| Electrical connection 1, type of mounting | Compatible with rotatable/non-rotatable screw-type lock |
| Electrical connection for input 1, connection pattern | 00991171 |
| Connection outlet orientation | Longitudinal |
| Material of pin contacts | Copper alloy, gold-plated |
| Connector cable test conditions | Flexural strength: as per Festo standard Torsion resistance: > 300,000 cycles, ±270°/0.1 m Energy chain: > 5 million cycles, bending radius 28 mm |
| Cable length | 0.3 m |
| Cable characteristic | suitable for energy chains/robot applications |
| Color cable sheath | Gray |
| Material of cable sheath | TPE-U(PUR) |
| Cable diameter | 2.9 mm |
| Type of mounting | Screwed tightly |
| Mounting position | Any |
| Product weight | 120 g |
| Housing colour | Black |
| Housing material | Polyester |
| Film material | Polyester |
| Switching status indication | LED yellow |
| Setting options | Pushbutton |
| Storage temperature | -30 °C ... 70 °C |
| Ambient temperature with flexible cable installation | -20 °C ... 70 °C |
| Degree of protection | IP65 IP68 |
| Protection class | III |
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |
| Vibration resistance | Transport application test with severity level 3 according to FN 942017-4 and EN 60068-2-6 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils. |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 4 according to ISO 14644-1 |