

# Parallel kit EAMM-U-70-D50-70A-96

Part number: 2786899

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	70
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	118 kgmm <sup>2</sup>
No-load driving torque	0.18 Nm
Transferable torque	7 Nm
Product weight	1700 g
Interface code, actuator	D50B
Interface code, motor in	70A
Note on materials	RoHS-compliant