

Right-angle clevis foot LQG-100

Part number: 31773

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	100
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	9 kN
Product weight	1493 g
Note on materials	RoHS-compliant
Mounting material	Spherulitic graphite iron
Bolt material	Case-hardened steel
Fuse material	Spring steel