

# Linear unit SLM-20- -KF-A

Part number: 32783

FESTO



 General operating condition

## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Stroke	10 mm ... 800 mm
Piston diameter	20 mm
Cushioning	Elastic cushioning rings/pads at both ends Pneumatic shock absorber, hard characteristic curve
Mounting position	Any
Guide	Recirculating ball bearing guide
Position sensing	For proximity sensor For inductive proximity sensors
Variants	Standard design Hollow guide rod Hollow guide rod and reversing plate
Operating pressure	0.7 MPa
Operating pressure	7 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C ... 60 °C
Theoretical force at 6 bar, retracting	188 N
Theoretical force at 6 bar, advancing	188 N
Moving mass	1400 g
Additional moving mass per 10 mm stroke	21 g
Basic weight with 0 mm stroke	2620 g
Additional weight per 10 mm stroke	21 g
Pneumatic connection	G1/8
Cover material	Aluminum
Seals material	PA TPE-U(PU)
Housing material	Aluminum