


# Control block CPX-CEC-M1-V3

Part number: 3472765

FESTO



 General operating condition

## Data sheet

Feature	Value
Protocol	CODESYS level 2 EasyIP Modbus® TCP TCP/IP
Dimensions W x L x H	50 mm x 107 mm x 55 mm
Product weight	135 g
Ambient temperature	-5 °C ... 50 °C
Storage temperature	-20 °C ... 70 °C
Relative air humidity	95% Non-condensating
Degree of protection	IP65 IP67
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS compliant
Housing material	PC
LED display (product-specific)	ERR: PLC runtime error M: Modify/force enabled PL: Load supply PS: electronics supply, sensor supply RUN: PLC status SF: System fault STOP: PLC status
LED display (bus-specific)	TP: Link/traffic
Device-specific diagnostics	Channel-oriented and module-oriented diagnostics Undervoltage/short circuit of modules Diagnostic memory
Control elements	DIL switch for CAN termination Rotary switch for RUN/Stop
IP address setting	DHCP Via CODESYS Via MMI
Fieldbus interface, type	CAN bus
Fieldbus interface, connection technology	Plug Sub-D 9-pin
Fieldbus interface, galvanic isolation	Yes
Fieldbus interface, transmission rate	125, 250, 500, 800, 1000 kbit/s Adjustable via software
Ethernet interface	RJ 45 (socket, 8-pin)
Ethernet, number	1

Feature	Value
Ethernet, supported protocols	TCP/IP, EasyIP, Modbus TCP
Ethernet, connector plug	RJ45 Bushing 8-pin
Ethernet, data transmission speed	10/100 mbps
Parameterization	CODESYS V3
Configuration support	CODESYS V3
Additional functions	SoftMotion functions for electric actuators
CPU data	800 MHz processor
Control interface	CAN bus
Nominal operating voltage DC	24 V
Nominal operating voltage DC load voltage	Without pneumatics: 18 ... 30V 24 V With midi/maxi pneumatic valves types: 21.6 ... 26.4 V With pneumatic type CPA: 20.4 ... 26.4 V With pneumatics type MPA: 18 ... 30 V
Intrinsic current consumption at nominal operating voltage	Type. 85 mA
Power failure buffering	10 ms
Programming, operating language	DE, EN
Programming language	As per IEC 61131-3 LDR SL items FBD SFC Additionally CFC
Programming, file handling support	Yes
Programming software	CODESYS provided by Festo
Program memory	16 MB user program
Processing time	Approx. 200 µs/1k commands
Function blocks	Read CPX module diagnostics CPX diagnostic status Copy CPX diagnostic trace and others
Flag	CODESYS variable concept
Total number of axes	31