

Limit switch box SRBG-C1-N-1-ZU-C2-C2

Part number: 3568166

FESTO



 General operating condition

Data sheet

Feature	Value
Design	Square
Based on norm	EN 60947-5-2 VDI/VDE 3845
Certification	CCC RCM compliance mark c UL us (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
KC characters	KC-EMV
Certificate issuing authority	2024010305706390
Note on materials	RoHS compliant
Measuring principle	Inductive
Ambient temperature	-25 °C ... 70 °C
Switching output	Non-contacting, 2-wire
Switching element function	N.O. contact
Max. switching frequency	500 Hz
Max. output current DC	100 mA
Voltage drop	≤6 V
Minimum load current	4 mA
Residual current	0 mA ... 1 mA
DC operating voltage range	6 V ... 60 V
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Terminal strip
Electrical connection 1, cable outlet	Straight
Electrical connection 1, design	Round
Electrical connection 1, connection technology	Spring-loaded terminal
Electrical connection 1, number of pins/wires	10
Electrical connection for input 1, connection pattern	00995595
Closable nominal conductor cross-section	0.2 mm ² ... 2.5 mm ²
Cable fitting	M20x1.5
Type of mounting	Screwed
Mounting position	Any
Product weight	170 g
Housing material	PBT
Material of screws	high-alloy stainless steel
Switching status indication	Yellow LED

Feature	Value
Status indicator	LED yellow = pneumatic valve switching status
Storage temperature	-25 °C ... 70 °C
Degree of protection	IP67
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
LABS (PWIS) conformity	VDMA24364 Zone III
Contamination level	3