

Limit switch box SRBE-CA3-YR90-MW-22A-2W-C2N12-C1

FESTO

Part number: 3998918



 [General operating condition](#)

Data sheet

Feature	Value
Design	Square
Based on norm	EN 60947-5-1 ISO 5211
CE marking (see declaration of conformity)	As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK instructions for electrical equipment
Explosion prevention and protection	Class I, Div. 1 (CA) Class I, Div. 1 (US) Class II, Div. 1 (CA) Class II, Div. 1 (US) Zone 1 (CA) Zone 1 (US) Zone 21 (CA) Zone 21 (US)
Type of ignition protection for gas	Ex d IIB T5 Gb
Type of (ignition) protection for dust	Ex tb IIIC T108°C Db
Explosion protection certification outside the EU	Class I, Div. 1 (CA) Class I, Div. 1 (US) Class II, Div. 1 (CA) Class II, Div. 1 (US) Class III (CA) Class III (US) EPL Db (CA) EPL Db (US) EPL Gb (CA) EPL Gb (US)
Certificate issuing authority	CSA 263311 Eurocert. SIL202587141
Note on materials	RoHS compliant
Safety integrity level (SIL)	SIL 3
Measuring principle	Mechanical/electrical Via proximity switch
Ambient temperature	-20 °C ... 60 °C
Switching output	Contact-based
Switching element function	Toggle switch, double-pin
Max. output current AC	3000 mA
Max. output current DC	6000 mA
Operating voltage range AC	0 V ... 230 V
DC operating voltage range	0 V ... 30 V
Microswitch type	Omron D3RV11
Electrical connection	Screw terminal

Feature	Value
Closable nominal conductor cross-section	0.25 mm ² ... 2.5 mm ²
Cable fitting	1/2 NPT
Type of mounting	on flange according to ISO 5211 With mounting bracket
Connection point for positioner and position sensor conforms to standard	VDI/VDE 3845 Size AA 1
Mounting position	Any
Product weight	1700 g
Housing colour	Silver
Housing material	Die cast aluminum, painted
Seals material	NBR
Shaft material	high-alloy stainless steel
Material of screws	high-alloy stainless steel
Material of mounting bracket	high-alloy stainless steel
Pointer material	PC
Circlip material	high-alloy stainless steel
Disc material	high-alloy stainless steel
Position indicator	Yellow/red
Angle detection setting range	0 deg ... 90 deg
Storage temperature	-20 °C ... 60 °C
Degree of protection	IP67 NEMA 4/4X
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
LABS (PWIS) conformity	VDMA24364 Zone III
Contamination level	3