


Axial kit EAMM-A-S95-100A-G2

FESTO

Part number: 3637955



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------|-----------------------|
| Nominal length | 85.5 mm |
| Mounting position | Any |
| Max. rotational speed | 5500 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 60 °C |
| Mass moment of inertia | 128 kgmm ² |
| Transferable torque | 60 Nm |
| Product weight | 2880 g |
| Interface code, actuator | S95 |
| Interface code, motor in | 100A |
| Note on materials | RoHS compliant |