

Ball valve VZBF-3/4-P1-20-D-2-F0304-V15V15

Part number: 4810852

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|--|
| Structural design | 2-way ball valve |
| Actuation type | Mechanical |
| Sealing principle | Soft |
| Mounting position | Any |
| Type of mounting | Line installation |
| Fitting connection | Flange as per ANSI B16.5 class 150 |
| Switching position indication | Slot direction = flow direction |
| Flange hole pattern | F0304 |
| Inside diameter | 20 mm |
| Nominal width DN | 20 |
| Valve function | 2/2 |
| Flow direction | Reversible |
| Nominal pressure of fitting PN | 20 |
| Breakaway torque at differential pressure, nominal pressure, fitting PN | 10 Nm |
| Based on norm | ISO 5211 |
| Symbol | 00991458 |
| Medium | Vapor Compressed air as per ISO 8573-1:2010 [:-:-] Inert gas Water Neutral liquids |
| Temperature of medium | -20 °C ... 200 °C |
| Flow rate Kv | 59 m ³ /h |
| Note on materials | RoHS-compliant |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Housing material | Cast stainless steel |
| Material number of housing | 1.4408 |

| Feature | Value |
|-------------------------------------|--|
| Seals material | FPM Graphite PCTFE PTFE |
| Ball material | Cast stainless steel |
| Material number for ball | 1.4408 |
| Shaft material | High-alloy stainless steel |
| Material number for shaft | 1.4401 |
| Product weight | 1950 g |
| Certification | API607 CRN |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Corrosion resistance class (CRC) | 4 - Particularly high corrosion stress |