

Compact cylinder AEN-S-63-10-I-P-A

Part number: 5132651

FESTO



 General operating condition

Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	63 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Pushing
Piston rod end	Internal thread
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Symbol	00991729
Variants	Piston rod at one end
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Operating pressure	14.5 psi ... 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 80 °C
Impact energy in the end positions	1.3 J
Theoretical force at 6 bar, retracting	69.9 N
Theoretical force at 6 bar, advancing	1780 N
Moving mass at 0 mm stroke	151 g
Additional moving mass per 10 mm stroke	16 g
Basic weight with 0 mm stroke	499 g
Additional weight per 10 mm stroke	77 g
Type of mounting	With through-hole With internal thread With accessories
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy, anodized
Material of dynamic seals	TPE-U(PU)
Housing material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy stainless steel