

# Round cylinder DSNU-S-20-25-P-A-MX

Part number: 5224636

FESTO



 General operating condition

## Data sheet

| Feature   | Value  |
|---|--|
| Stroke  | 25 mm  |
| Piston diameter   | 20 mm  |
| Piston rod thread   | M8   |
| Cushioning  | Elastic cushioning rings/pads at both ends                         |
| Mounting position   | Any  |
| Structural design   | Piston<br>Piston rod<br>Cylinder barrel                            |
| Position sensing  | For proximity sensor   |
| Symbol  | 00991217   |
| Operating pressure  | 0.08 MPa ... 1 MPa   |
| Operating pressure  | 0.8 bar ... 10 bar   |
| Mode of operation   | Double-acting  |
| Operating medium  | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media                  | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)                          | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                                    | VDMA24364-B2-L   |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 5 according to ISO 14644-1                                   |
| Ambient temperature                                       | -20 °C ... 80 °C   |
| Impact energy in the end positions                        | 0.2 J  |
| Theoretical force at 6 bar, retracting                    | 158.3 N  |
| Theoretical force at 6 bar, advancing                     | 188.5 N  |
| Moving mass at 0 mm stroke                                | 37.3 g   |
| Additional moving mass per 10 mm stroke                   | 4 g  |
| Basic weight with 0 mm stroke                             | 126 g  |
| Additional weight per 10 mm stroke                        | 7.2 g  |
| Type of mounting  | With accessories   |
| Pneumatic connection                                      | G1/8   |
| Note on materials   | RoHS-compliant   |
| Cover material  | Wrought aluminum alloy, anodized                                   |
| Seals material  | TPE-U(PU)  |
| Piston rod material                                       | High-alloy stainless steel   |
| Material of cylinder barrel                               | High-alloy stainless steel   |