

Vacuum generator VN-05-M-T2-PQ1-VQ1-RQ1

Part number: 526106

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|---|
| Nominal width of Laval nozzle | 0.45 mm |
| Width dimension | 10 mm |
| Mounting position | Any |
| Ejector characteristics | High vacuum Inline |
| Structural design | T-shape |
| Symbol | 00991491 |
| Operating pressure for max. suction rate | 6.3 bar |
| Operating pressure | 1 bar ... 8 bar |
| Operating pressure for max. vacuum | 6 bar |
| Max. vacuum | 86 % |
| Nominal operating pressure | 6 bar |
| Max. suction rate with respect to atmosphere | 6.1 l/min |
| Air supply time at nominal operating pressure | 4.7 s |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication not possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | 0 °C ... 60 °C |
| Ambient temperature | 0 °C ... 60 °C |
| Max. tightening torque | 0.5 Nm |
| Product weight | 15 g |
| Type of mounting | With through-hole With accessories |
| Pneumatic connection 1 | QS-4 |
| Pneumatic connection 3 | QS-4 |
| Vacuum connection | QS-4 |
| Note on materials | RoHS-compliant |
| Seals material | NBR |
| Female nozzle material | POM |
| Housing material | POM-reinforced |
| Material of jet nozzle | Wrought aluminum alloy |
| Material of pneumatic fitting | Brass Nickel-plated |