


Vacuum generator VN-07-M-T2-PI2-VI2-RI2

FESTO

Part number: 526111



[PDF](#) General operating condition

Data sheet

Feature	Value
Nominal width of Laval nozzle	0.7 mm
Width dimension	10 mm
Mounting position	Any
Ejector characteristics	High vacuum Inline
Structural design	T-shape
Symbol	00991491
Operating pressure for max. suction rate	7 bar
Operating pressure	1 bar ... 8 bar
Operating pressure for max. vacuum	5.8 bar
Max. vacuum	86 %
Nominal operating pressure	6 bar
Max. suction rate with respect to atmosphere	13.5 l/min
Air supply time at nominal operating pressure	2.1 s
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	0 °C ... 60 °C
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	0.5 Nm
Product weight	13 g
Type of mounting	With through-hole With accessories
Pneumatic connection 1	M5
Pneumatic connection 3	M5
Vacuum connection	M5
Material of connecting thread	Wrought aluminum alloy, anodized
Note on materials	RoHS compliant
Seals material	NBR
Female nozzle material	POM
Housing material	Reinforced POM
Material of jet nozzle	Wrought aluminum alloy