

Fine filter MS6-LFM-1/2-BRM

Part number: 529659

FESTO



 General operating condition

Data sheet

Feature	Value
Series	MS
Size	6
Structural design	Fiber filter
Grade of filtration	1 µm
Condensate drain	Manual, rotating
Symbol	00991519
Operating pressure	0 MPa ... 2 MPa
Operating pressure	0 bar ... 20 bar
Operating pressure	0 psi ... 290 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [6:::4] Inert gases
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [5:::3]
Max. standard flow rate for air quality class	950 l/min
Min. standard flow rate for air quality class	140 l/min
Filter efficiency	99.99 %
Max. condensate volume	38 ml
Bowl guard	Plastic bowl guard
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
For use in the food industry	See supplementary material information
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Storage temperature	-10 °C ... 60 °C
Filter efficiency, fine particles	99 %
Residual oil content	0.5 mg/m ³
Filter efficiency, oil aerosol	90 %
Type of mounting	With accessories
Mounting position	Vertical ±5°
Pneumatic connection 1	G1/2
Pneumatic connection 2	G1/2
Housing material	Die-cast aluminum
Compressed air filter material	Borosilicate glass fiber
Material of bowl	PC
Seals material	NBR

Feature	Value
Note on materials	RoHS compliant
Product weight	600 g