

# Filter MS6N-LF-3/8-CUM

Part number: 531539

FESTO



General operating condition

## Data sheet

Feature	Value
Size	6
Series	MS
Mounting position	Vertical $\pm 5^\circ$
Grade of filtration	5 $\mu\text{m}$
Condensate drain	Manual, rotating
Structural design	Sinter filter with centrifugal separator
Bowl guard	Integrated as metal bowl
Degree of condensate separation	$>75\%$
Symbol	00991519
Operating pressure	0 bar ... 20 bar
Normal nominal flow rate (normalized to DIN 1343)	3000 l/min
Operating medium	Inert gases
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 $^\circ\text{C}$ ... 60 $^\circ\text{C}$
For use in the food industry	See supplementary material information
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [6:8:4]
Temperature of medium	-10 $^\circ\text{C}$ ... 60 $^\circ\text{C}$
Ambient temperature	-10 $^\circ\text{C}$ ... 60 $^\circ\text{C}$
Pore size	$<5\ \mu\text{m}$
Product weight	820 g
Type of mounting	With accessories
Pneumatic connection 1	3/8 NPT
Pneumatic connection 2	3/8 NPT
Note on materials	RoHS compliant
Seals material	NBR
Compressed air filter material	Protective grounding
Housing material	Die-cast aluminum
Material of bowl	Wrought aluminum alloy
Separating disc material	POM