

Parallel gripper HGPP-32-A

Part number: 525664

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Size	32
Stroke per gripper jaw	12.5 mm
Max. interchangeability	0.1 mm
Max. gripper jaw angular play ax, ay	0 deg
Max. gripper jaw backlash Sz	0 mm
Rotational symmetry	0.05 mm
Pneumatic gripper repetition accuracy	≤0.02 mm
Number of gripper jaws	2
Actuator system	Pneumatic
Mode of operation	Double-acting
Gripper function	Parallel
Gripping force backup	None
Structural design	Gear rack/pinion
Position sensing	For Hall sensor For inductive sensors
Symbol	00991894
Operating pressure	2 bar ... 8 bar
Max. operating frequency of pneumatic gripper	4 Hz
Min. opening time at 6 bar	76 ms
Min. closing time at 6 bar	110 ms
Max. mass per external gripper finger	300 g
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	5 °C ... 60 °C
Gripping force per gripper jaw at 6 bar, opening	830 N
Gripping force per gripper jaw at 6 bar, closing	830 N
Gripping force per gripper jaw at 6 bar, opening	415 N
Gripping force per gripper jaw at 6 bar, closing	415 N
Mass moment of inertia	38.34 kgcm ²
Maximum force on gripper jaw Fz, static	720 N
Maximum torque on gripper jaw, Mx static	30 Nm
Maximum torque on gripper jaw, My static	30 Nm
Maximum torque on gripper jaw, Mz static	30 Nm

Feature	Value
Product weight	1408 g
Type of mounting	With internal thread
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Cover cap material	POM
Housing material	Wrought aluminum alloy, hard-anodized
Gripper jaw material	Wrought aluminum alloy, nickel-plated