


Vacuum generator VN-20-L-T6-PI5-VI6-RO2

Part number: 526131

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|---|
| Nominal width of Laval nozzle | 2 mm |
| Width dimension | 24 mm |
| Muffler construction type | Open |
| Mounting position | Any |
| Ejector characteristics | High suction rate Standard |
| Integrated function | Pneumatic muffler open |
| Structural design | T-shape |
| Symbol | 00991489 |
| Operating pressure for max. suction rate | 3 bar |
| Operating pressure | 1 bar ... 8 bar |
| Nominal operating pressure | 6 bar |
| Max. suction rate with respect to atmosphere | 188 l/min |
| Air supply time at nominal operating pressure | 0.15 s |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication not possible |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Temperature of medium | 0 °C ... 60 °C |
| Noise level at nominal operating pressure | 60 dB(A) |
| Ambient temperature | 0 °C ... 60 °C |
| Max. tightening torque | 0.8 Nm |
| Product weight | 183 g |
| Type of mounting | With through-hole With accessories |
| Pneumatic connection 1 | G1/4 |
| Pneumatic connection 3 | Pneumatic muffler open |
| Vacuum connection | G3/8 |
| Material of connecting thread | Wrought aluminum alloy, anodized |
| Note on materials | RoHS-compliant |
| Seals material | NBR |
| Female nozzle material | POM |
| Housing material | POM-reinforced |
| Muffler material | Die-cast aluminum POM PU foam |
| Material of jet nozzle | Wrought aluminum alloy |