

On/off valve MS6N-EE-1/2-V230

Part number: 532116

FESTO



General operating condition

Data sheet

| Feature | Value |
|---|--|
| Structural design | Piston gate valve |
| Actuation type | Electrical |
| Exhaust air function | Cannot be throttled |
| Manual override | Detenting Non-detenting |
| Reset method | Mechanical spring |
| Type of control | Piloted |
| Symbol | 00991008 |
| Valve function | 3/2-way, closed, monostable |
| Operating pressure | 4 bar ... 18 bar |
| C value | 29 l/sbar |
| b-value | 0.4 |
| Normal nominal flow rate (normalized to DIN 1343) | 7000 l/min |
| Duty cycle | 100% |
| Coil characteristics | 230 V AC: 50/60 Hz, initial power 3.0 VA, holding power 2.4 VA |
| Permissible voltage fluctuations | -14% / +10% |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Note on materials | RoHS compliant |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Temperature of medium | -10 °C ... 60 °C |
| Degree of protection | IP65 |
| Ambient temperature | -10 °C ... 60 °C |
| For use in the food industry | See supplementary material information |
| Type of mounting | Alternatively: In-line installation With accessories |
| Mounting position | Any |
| Flow direction | Non-reversible |
| Product weight | 740 g |
| Pneumatic connection 1 | 1/2 NPT |
| Pneumatic connection 2 | 1/2 NPT |
| Pneumatic connection 3 | G1/2 |
| Pilot air supply port | Internal |

| Feature | Value |
|-----------------------|--|
| Electrical connection | Type C Plug As per DIN EN 175301-803 Rectangular design |
| Seals material | NBR |
| Housing material | Die-cast aluminum |