

Fine filter LFMB-1/2-D-MIDI-DA-A

Part number: 532832

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Series | D |
| Size | Midi |
| Structural design | Fiber filter |
| Grade of filtration | 1 µm |
| Condensate drain | Fully automatic |
| Symbol | 00991544 |
| Operating pressure | 0.2 MPa ... 1.2 MPa |
| Operating pressure | 2 bar ... 12 bar |
| Operating pressure | 29 psi ... 174 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [6:4:4] Inert gases |
| Air quality class at the output | Compressed air according to ISO 8573-1:2010 [5:4:3] Inert gases |
| Max. standard flow rate for air quality class | 1750 l/min |
| Min. standard flow rate for air quality class | 500 l/min |
| Filter efficiency | 99.99 % |
| Max. condensate volume | 43 ml |
| Bowl guard | Metal bowl guard |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | 1.5 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Storage temperature | -10 °C ... 60 °C |
| Filter efficiency, fine particles | 99 % |
| Residual oil content | 0.5 mg/m ³ |
| Filter efficiency, oil aerosol | 90 % |
| Differential pressure display | Visual display |
| Type of mounting | With accessories |
| Mounting position | Vertical ±5° |
| Pneumatic connection 1 | G1/2 |
| Pneumatic connection 2 | G1/2 |
| Housing material | Die-cast zinc |
| Compressed air filter material | Borosilicate glass fiber |

| Feature | Value |
|-------------------|----------------|
| Material of bowl | PC |
| Note on materials | RoHS compliant |
| Product weight | 834 g |