

# Air preparation combination unit MSB6-1/2-FRC7:J3M1

Part number: 530248

FESTO



## Data sheet

 General operating condition

Feature	Value
Size	6
Series	MS
Actuator lock	Rotary knob with integrated lock
Mounting position	Vertical $\pm 5^\circ$
Condensate drain	Manual, rotating
Structural design	Proportional standard oil mist lubricator
Grade of filtration	5 $\mu\text{m}$
Controller function	Constant output pressure With primary pressure compensation With secondary exhausting With return flow characteristic
Bowl guard	Plastic bowl guard
Symbol	00991761
Pressure gauge	with pressure gauge
Operating pressure	1.5 bar ... 20 bar
Pressure regulation range	0.5 bar ... 12 bar
Normal nominal flow rate (normalized to DIN 1343)	3600 l/min
Operating medium	Inert gases
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
For use in the food industry	See supplementary material information
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [6:4:-]
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	1495 g
Type of mounting	With accessories
Pneumatic connection 1	G1/2
Pneumatic connection 2	G1/2
Note on materials	RoHS compliant