

Air preparation combination unit MSB6-1/2-FRC9:J11M2

Part number: 530252

FESTO



 General operating condition

Data sheet

Feature	Value
Size	6
Series	MS
Actuator lock	Rotary knob with integrated lock
Mounting position	Vertical +/- 5°
Condensate drain	Manually rotating
Structural design	Proportional standard oil mist lubricator
Grade of filtration	40 µm
Controller function	Outlet pressure constant With primary pressure compensation With secondary exhausting With return flow function
Bowl guard	Integrated as metal bowl guard
Symbol	00991761
Pressure gauge	with pressure gauge
Operating pressure	1.5 bar ... 20 bar
Pressure regulation range	0.5 bar ... 12 bar
Normal nominal flow rate (normalized to DIN 1343)	3700 l/min
Operating medium	Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
For use in the food industry	See supplementary material information
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:4:-]
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	1713 g
Type of mounting	With accessories
Pneumatic connection 1	G1/2
Pneumatic connection 2	G1/2
Note on materials	RoHS-compliant