

Air preparation combination unit MSB4N-1/8-FRC6:J2M1

Part number: 533973

FESTO



 General operating condition

Data sheet

Feature	Value
Size	4
Series	MS
Actuator lock	Rotary knob with integrated lock
Mounting position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	Fully automatic
Structural design	Proportional standard oil mist lubricator
Controller function	Outlet pressure constant With primary pressure compensation With secondary exhausting With return flow function
Bowl guard	Plastic bowl guard
Symbol	00991599
Pressure gauge	with pressure gauge
Operating pressure	1.5 bar ... 12 bar
Pressure regulation range	1 bar ... 12 bar
Normal nominal flow rate (normalized to DIN 1343)	850 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:-] Inert gases
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
For use in the food industry	See supplementary material information
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:4:-]
Temperature of medium	5 °C ... 60 °C
Ambient temperature	5 °C ... 60 °C
Product weight	500 g
Type of mounting	With accessories
Pneumatic connection 1	1/8 NPT
Pneumatic connection 2	1/8 NPT
Housing material	Die-cast aluminum
Material of bowl	PC