

# Active carbon filter LFX-1/4-D-MINI

Part number: 532802

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	Mini
Series	D
Mounting position	Vertical +/- 5°
Structural design	Active carbon filter Fiber filter
Bowl guard	Metal bowl guard
Symbol	00991519
Operating pressure	0 MPa ... 1.6 MPa
Operating pressure	0 bar ... 16 bar
Operating pressure	0 psi ... 232 psi
Recommended maximum standard flow	360 l/min
Max. standard flow rate for air quality class	360 l/min
Operating medium	Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [1:4:1] Inert gas
Temperature of medium	5 °C ... 30 °C
Residual oil content	≤0.003 mg/m <sup>3</sup>
Ambient temperature	-10 °C ... 60 °C
Product weight	376 g
Type of mounting	With mounting bracket
Pneumatic connection	G1/4
Pneumatic connection 1	Sub-base G1/4
Pneumatic connection 2	Sub-base G1/4
Note on materials	RoHS-compliant
Compressed air filter material	Activated carbon Fabric
Housing material	Die-cast zinc
Material of bowl	PC