

Micro filter LFMA-1/4-D-MINI-DA-A

Part number: 532854

FESTO



 General operating condition

Data sheet

Feature	Value
Series	D
Size	Mini
Structural design	Fiber filter
Grade of filtration	0.01 µm
Condensate drain	Fully automatic
Symbol	00991544
Operating pressure	0.2 MPa ... 1.2 MPa
Operating pressure	2 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:4:4] Inert gases
Air quality class at the output	Compressed air according to ISO 8573-1:2010 [3:4:2] Inert gases
Max. standard flow rate for air quality class	410 l/min
Min. standard flow rate for air quality class	100 l/min
Filter efficiency	99.9999 %
Bowl guard	Metal bowl guard
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	1.5 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Filter efficiency, fine particles	99995 %
MPPS	0.05 µm
MPPS filter efficiency	99.95 %
Residual oil content	0.01 mg/m ³
Filter efficiency, oil aerosol	99 %
Differential pressure display	Visual display
Type of mounting	With accessories
Mounting position	Vertical ±5°
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Housing material	Die-cast zinc
Compressed air filter material	Borosilicate glass fiber
Material of bowl	PC

Feature	Value
Note on materials	RoHS compliant
Product weight	368 g