

Handling module HSP-16-AS

Part number: 533613

FESTO



 General operating condition

Data sheet

Feature	Value
Size	16
Y-stroke	90 mm ... 110 mm
Z-stroke	35 mm ... 50 mm
Z working stroke	20 mm
Cushioning	Acoustic insulation via buffers
Mounting position	Guide rail Vertical
Structural design	Cross guide Positively driven motion sequence
Position sensing	Via proximity switch
Protection against torsion/guide	Cross guide
Minimum cycle time	0.8 s
Repetition accuracy	±0.01 mm
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Max. driving torque on actuator shaft	2.5 Nm
Max. axial force at actuator shaft	30 N
Max. torque Mx dynamic	2.4 Nm
Max. static moment Mx	10 Nm
Max. torque My dynamic	2.4 Nm
Max. static moment My	10 Nm
Max. torque Mz dynamic	2.4 Nm
Max. static moment Mz	10 Nm
Max. payload	1 kg
Max. radial force on actuator shaft	75 N
Maximum process force in y direction	35 N
Theoretical force at 6 bar	50 N
Product weight	3100 g
Front unit mounting	With through-hole
Type of mounting	With through-hole With slot nuts
Stops material	High-alloy steel
Spring pressure piece material	High-alloy steel
Base plate material	Wrought aluminum alloy
Retainer bracket material	Wrought aluminum alloy
Cross guide material	Quenched and tempered steel

Feature	Value
Swivel lever material	Case-hardened steel Burnished
Link material	Case-hardened steel Burnished
Side covers material	Wrought aluminum alloy
Sensor rail material	Wrought aluminum alloy Anodized
Fixed link material	Wrought aluminum alloy Anodized
Setting screw material	High-alloy steel