

Handling module HSP-25-AS-SD

Part number: 533622

FESTO



 General operating condition

Data sheet

Feature	Value
Size	25
Y-stroke	130 mm ... 170 mm
Z-stroke	50 mm ... 70 mm
Z working stroke	25 mm
Cushioning	Acoustic insulation via buffers
Mounting position	Guide rail Vertical
Structural design	Cross guide Positively driven motion sequence
Position sensing	Via proximity switch
Protection against torsion/guide	Cross guide
Minimum cycle time	1 s
Repetition accuracy	±0.02 mm
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Max. driving torque on actuator shaft	5 Nm
Max. axial force at actuator shaft	50 N
Max. torque Mx dynamic	3.2 Nm
Max. static moment Mx	15 Nm
Max. torque My dynamic	3.2 Nm
Max. static moment My	15 Nm
Max. torque Mz dynamic	3.2 Nm
Max. static moment Mz	15 Nm
Max. payload	1.5 kg
Max. radial force on actuator shaft	120 N
Maximum process force in y direction	50 N
Theoretical force at 6 bar	65 N
Product weight	7400 g
Front unit mounting	With through-hole
Type of mounting	With through-hole With slot nuts
Stops material	High-alloy steel
Cover material	Wrought aluminum alloy, anodized
Spring pressure piece material	High-alloy steel
Base plate material	Wrought aluminum alloy
Retainer bracket material	Wrought aluminum alloy

Feature	Value
Cross guide material	Quenched and tempered steel
Swivel lever material	Case-hardened steel Burnished
Link material	Case-hardened steel Burnished
Side covers material	Wrought aluminum alloy
Sensor rail material	Wrought aluminum alloy Anodized
Fixed link material	Wrought aluminum alloy Anodized
Setting screw material	High-alloy steel