


Fine filter MS4-LFM-1/4-BUV

Part number: 535766

FESTO



 General operating condition

Data sheet

Feature	Value
Series	MS
Size	4
Structural design	Fiber filter
Grade of filtration	1 µm
Condensate drain	Manual, non-detenting
Symbol	00991520
Operating pressure	0.2 MPa ... 1.2 MPa
Operating pressure	2 bar ... 12 bar
Operating pressure	29 psi ... 174 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [6:::4] Inert gases
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [5:::3]
Max. standard flow rate for air quality class	360 l/min
Min. standard flow rate for air quality class	54 l/min
Filter efficiency	99.99 %
Max. condensate volume	25 ml
Bowl guard	Integrated as metal bowl
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
For use in the food industry	See supplementary material information
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Storage temperature	-10 °C ... 60 °C
Filter efficiency, fine particles	99 %
Residual oil content	0.5 mg/m ³
Filter efficiency, oil aerosol	90 %
Type of mounting	With accessories
Mounting position	Vertical ±5°
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Housing material	Die-cast aluminum
Compressed air filter material	Borosilicate glass fiber
Material of bowl	Die-cast aluminum Wrought aluminum alloy
Inspection window material	PA

Feature	Value
Seals material	NBR
Note on materials	RoHS compliant
Product weight	350 g